C ICHIGUCHI

Flap Wheel with shaft

Applications

- ●Polishing inner surfaces of pipes ●Rounding edges, hole borders ●Deburring
- ●Removing burn marks after welding ●Polishing narrow secluded corners and curved surfaces

Flap Wheel



- The highly flexible wheel with a shaft is a standard product.
- Abrasive material is quickly discharged after being scraped, leaving the polishing power stably high.



Micro Flap



Suited to smooth operations on fine gaps, with no axial runout under high-speed rotations.





Flap Wheel • Aluminum oxide(A)



item no.	dia x width(mm)	shaft dia x length(mm)	RPM	grit														Q'ty/	
	ula x wiutii(iiiiii)			24	36	40	60	80	100	120	150	180	240	320	400	600	800	1000	
AF2505	25 x 5	3×35	20,000r.p.m.				•	•	•	•	•	•	•	•	•				5
AF2525	25 x 25	6 × 40	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF3005	30 x 5	3 x 35	20,000r.p.m.				•	•	•	•	•	•	•	•	•				5
AF30103	30 x 10	3 x 35	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF30106	30 x 10	6 × 40	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF3015	30 x 15	6 x 40	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF3025	30 x 25	6 × 40	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF4005	40 x 5	6 x 40	20,000r.p.m.				•	•	•	•	•	•	•	•	•				5
AF4015	40 x 15	6 × 40	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF4025	40 x 25	6 x 40	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF4030	40×30	6 × 40	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF5005	50 x 5	6 x 40	20,000r.p.m.				•	•	•	•	•	•	•	•	•				5
AF5015	50 x 15	6 × 40	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF5025	50 x 25	6 × 40	20,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF5030	50 x 30	6 × 40	18,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF6005	60 x 5	6 × 40	18,000r.p.m.				•	•	•	•	•	•	•	•	•				5
AF6015	60 x 15	6 x 40	18,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF6025	60 x 25	6 × 40	18,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF6030	60 x 30	6 x 40	18,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF8005	80 x 5	6×40	15,000r.p.m.				•	•	•	•	•	•	•	•	•				5
AF8015	80 x 15	6 x 40	15,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5
AF8025	80 x 25	6 × 40	15,000r.p.m.			•	•	•	•	•	•	•	•	•	•	•			5

Micro Flap ● Aluminum oxide(A)



itama ma	dia x width(mm)	shaft dia x length(mm)	RPM		grit														Q'ty/
item no.				24	36	40	60	80	100	120	150	180	240	320	400	600	800	1000	
MF1005	10 x 5	3×30	25,000r.p.m.				•	•	•	•	•	•	•	•	•				10
MF1010	10 x 10	3 x 30	25,000r.p.m.				•	•	•	•	•	•	•	•	•	•			10
MF1505	15 x 5	3 x 30	25,000r.p.m.				•	•	•	•	•	•	•	•	•				10
MF1510	15 x 10	3 x 30	25,000r.p.m.				•	•	•	•	•	•	•	•	•	•			10
MF2005	20 x 5	3 x 30	20,000r.p.m.				•	•	•	•	•	•	•	•	•				10
MF2010	20 x 10	3 x 30	20,000r.p.m.				•	•	•	•	•	•	•	•	•	•			10